

USB Type-C™ Docking Station 8K - HDMI / USB / PD 3.0 100 W

Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3 or Thunderbolt™ 4 port and provides a variety of interfaces. A monitor can be operated at the HDMI output port by a maximum resolution up to **8K Ultra HD (7680 x 4320 @ 30 Hz)**. **Two built-in USB Type-A and one USB-C™ port** allow the use of peripherals.



USB Power Delivery (USB PD 3.0) support up to 100 watt

The docking station has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 100 watts during operation.

Item no. 87804

EAN: 4043619878048

Country of origin: China

Package: Retail Box

Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 2 x USB 5 Gbps Type-A female
 - 1 x USB 5 Gbps USB Type-C™ female
 - 1 x HDMI-A female
 - 1 x USB Type-C™ PD female (power supply)
- Resolution up to 7680 x 4320 @ 30 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports HDCP 1.4 and 2.2
- Supports HDR
- Output power for host: max. 100 W
- Metal housing
- Cable length without connectors: ca. 15 cm
- Colour: grey
- Dimensions (LxWxH): ca. 97 x 37 x 10 mm

System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.11 or above
- Mac OS 12.2.1 or above
- Windows 8.1/8.1-64/10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- USB-C™ docking station
- User manual

Images



General

Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 5.11 or above Mac OS 12.2.1 or above Android 11.0 or above
-----------------------------	---

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI-A female
Connector 3:	2 x USB 5 Gbps Type-A female
Connector 4:	1 x USB 5 Gbps USB Type-C™ female

Technical characteristics

Maximum screen resolution:	7680 x 4320 @ 30 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	Aluminium
Cable length:	15 cm
Length:	97 mm
Width:	37 mm
Height:	10 mm
Colour:	grey

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de