

4 Port USB 10 Gbps Hub with USB Type-C™ connector 60 cm Cable and Switch for each port

Description

This solid USB hub by Delock with metal housing can be connected to a computer, laptop or mobile device via the **USB-C™** interface. It expands the computer by **4 USB Type-A ports**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected. Each port can be turned on or off individually by using the switches.

Supports USB 10 Gbps

A maximum data transfer rate of up to **10 Gbps** can be reached.

Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock Hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 64233

EAN: 4043619642335

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 4 x USB 10 Gbps Type-A female
 - 1 x 5 V DC jack
- Chipset: VIA VL822
- Data transfer rate up to 10 Gbps
- 4 x LED indicator
- 4 x switch
- Robust metal housing
- Dimensions (LxWxH): ca. 98 x 39 x 22 mm
- Cable length: ca. 60 cm
- Colour: black
- Plug & Play

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: ABT020050BEU
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz

- Input current: 0.5 A
 - Output voltage / Output current / Output power: 5.0 V / 2.0 A / 10.0 W
 - Average active efficiency: 79.4 %
 - No-load power consumption: 0.06 W
 - Cable length of power supply: ca. 0.5 m
 - Ground outside, plus inside
 - Dimensions:
 - inside: \varnothing ca. 1.35 mm
 - outside: \varnothing ca. 3.5 mm
 - Length: ca. 7 mm
-

System requirements

- Android 11.0 or above
 - Chrome OS
 - Linux Kernel 5.15 or above
 - Mac OS 12.4 or above
 - Windows 8.1/8.1-64/10/10-64/11
 - iPad Air (4th Generation) or above
 - iPad Pro (3rd Generation) or above
 - Surface Pro 7
 - Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port or
 - Device with a free USB4™ port or with a free Thunderbolt™ 4 port
-

Package content

- Hub USB 10 Gbps
- External power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 12.4 oder höher Android 11.0 or above Linux Kernel 5.15 or above
LED indicator:	4 x

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	4 x USB 10 Gbps Type-A female
Connector 3:	1 x DC jack

Technical characteristics

Chipset:	VIA VL822
Data transfer rate:	10 Gbps

Physical characteristics

Material:	metal
Length:	98 mm
Width:	39 mm
Height:	22 mm
Colour:	black

Power supply

Power supply type:	Power supply specification Euro wall power supply
Model identifier:	Power supply specification ABT020050BEU
Input voltage:	Power supply specification 100 - 240 V
Input AC frequency:	Power supply specification 50 / 60 Hz
Input current:	Power supply specification 0.5 A
Output voltage / Output current / Output power:	Power supply specification 5.0 V / 2.0 A / 10.0 W
Average active efficiency:	Power supply specification 79.4 %
No-load power consumption:	Power supply specification 0.06 W
Power supply connector:	Power supply specification DC male 3.5 mm x 1.35 mm Ground outside, plus inside
Cable length of power supply:	Power supply specification 0.5 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de