

USB Docking Station for 3 x SATA HDD / SSD with 1:2 Clone Function

Description

This docking station by Delock enables an external connection of up to **three 2.5" or 3.5" SATA HDDs or SSDs** through the USB interface. This solution does not require an external enclosure since the drive can just plug in directly into the docking station.

Clone Function

The clone function enables to copy the content of **one HDD to one or two drives** without using a PC.



Item no. 64332

EAN: 4043619643325

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 3 x SATA 6 Gb/s 22 pin receptacle
 - 1 x DC jack
- Chipset: JMicron JMS562
- Function key:
 - 1 x Clone button
 - 1 x On / Off switch
- For 2.5" and 3.5" SATA HDD / SSD
- Suitable for all SATA HDDs up to SATA 6 Gb/s
- Data transfer rate up to 5 Gbps
- LED indicator for power, access and copy status
- Bootable
- Dimensions (LxWxH): ca. 139 x 121 x 69 mm
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 1.5 A
- Output: 12.0 V / 4.0 A / 48.0 W

- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 10 mm

System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.5 or above
- Mac OS 14.5 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- PC or laptop with a free USB Type-A port

Package content

- Docking station
- Cable USB Type-A male to Type-B male, length ca. 1 m
- External power supply
- User manual

Images



General

Function:	Plug & Play Clone Function
Suitable for data medium:	2.5" 3.5" SSD or HDD
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit iPad Air (4th Generation) or above Windows 11 Android 14.0 or above Linux Kernel 6.5 or above Mac OS 14.5 or above
LED indicator:	power, access and copy status

Interface

External:	1 x DC jack 1 x USB 5 Gbps Type-B female
Internal:	3 x SATA 6 Gb/s 22 pin receptacle

Technical characteristics

Chipset:	JMicron JMS562
Data transfer rate:	5 Gbps

Physical characteristics

Housing material:	Plastic
Length:	139 mm
Width:	121 mm
Height:	69 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de