

# USB Type-C™ Slim Docking Station 4K - HDMI / USB 3.2 Gen 1 / LAN / SD / PD 3.0

## Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3 port and provides a variety of interfaces. A monitor can be operated at the **HDMI** output. **Four built-in USB ports** allow the use of peripherals, and connections for **SD and Micro SD** card and **Gigabit network** complete the features.

### USB Power Delivery (USB PD 3.0) support up to 85 watt

The docking station has a USB Type-C™ Power Delivery port. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to **85 watts** during operation.

### Use under the laptop

Due to its elongated shape and **metal housing**, the docking station is perfectly suited for use under a laptop, e.g. MacBook. The increased tilt of the laptop serves a better comfort while working, as well as a **better cooling of the laptop**.



**Item no. 87895**

EAN: 4043619878956

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ female
  - 1 x USB Type-C™ female (power supply)
  - 4 x USB 5 Gbps Type-A female
  - 1 x HDMI female
  - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
  - 1 x SD / SDHC / SDXC / MMC slot
  - 1 x Micro SD / SDHC / SDXC slot
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- It can be used two memory cards at the same time
- Data can be exchanged directly between two connected memory cards
- USB Power Delivery (PD) 3.0
- Supports HDCP 1.4
- Output power for host: max. 85 W
- 1 x LED indicator

- Metal housing
- Colour: grey
- Dimensions (LxWxH): ca. 282 x 41 x 16 mm

---

## System requirements

- Mac OS 12.4 or above
- Windows 8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ docking station
- Cable USB-C™ male to USB-C™ male, length ca. 20 cm
- User manual

---

## Images



## General

Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Mac OS 12.4 oder höher
LED indicator:	1 x

## Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

## Physical characteristics

Cable length:	20 cm (without connector)
Length:	282 mm
Width:	41 mm
Height:	16 mm
Colour:	grey

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de