

Antenna WiFi 6 RP-SMA plug 3 dBi omnidirectional with connection cable RG-174 3 m with tilt joint with magnetic base black

Description

This WiFi 6 antenna by Delock allows the usage of WiFi frequency range indoors.



Item no. 10039

EAN: 4043619100392

Country of origin: China

Package: Box

Technical details

- Connector: 1 x RP-SMA plug
- Frequency range:
2.400 GHz - 2.483 GHz
5.150 GHz - 5.850 GHz
- Antenna gain: 3 dBi
- Impedance: 50 Ohm
- VSWR: 2.0
- Cable type: RG-174
- Cable attenuation: 0.9 dB @ 800 MHz per meter
- Cable colour: black
- Cable length: ca. 3 m
- Polarisation: linear, vertical
- Operating temperature: -40 °C ~ 70 °C
- Housing material: ABS
- Colour: black
- Dimensions:
antenna (LxWxH): ca. 174 x 18 x 13 mm
base (DxH): ca. 61.0 x 30.8 mm

System requirements

- Device with a free RP-SMA jack

Package content

- Antenna

General

Mounting type:	magnetic
Suitable for indoor:	yes

Interface

Connector:	1 x RP-SMA plug
------------	-----------------

Technical characteristics

Frequency range:	5150 - 5850 MHz 2400 - 2483 MHz
Antenna gain:	3 dBi
Impedance:	50 Ohm
Operating temperature:	-40 °C ~ 70 °C
VSWR:	2.0

Physical characteristics

Antenna type:	dipol antenna
Cable type:	RG-174
Cable colour:	black
Cable length:	3 m
Length:	174 mm
Width:	18 mm
Height:	13 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail

info@delock.de

Website

www.delock.de

