



BETA 7270Y

FitEVOLUTION mesh fabric shoe, highly breathable



Certifications and Standards



S1PS FO SR ESD

EN ISO 20345:2022

Features

The 7270Y model is the perfect synthesis of lightness and functionality: neon yellow outsole and details enhance the comfort of the mesh upper.

FIT4YOU system

Create your own comfort with BETA's patented FIT4YOU system: a special cavity in the penetration proof insole allows you to replace the ETPU insole at any time, choosing from three different densities included in the pack.

ETPU inserts

ETPU is known for its excellent anti-shock and shock-absorbing properties. The three inserts soft, intermediate and rigid make it easy and immediate to customise the softness and support of the shoe to suit your needs.

Breathable and resistant

The mesh upper is incredibly lightweight thanks to the open weave that promotes air circulation. It is also surprisingly durable, ideal for shoes built to last, without compromising on quality.

Metal-free

Composite toe cap and midsole are made of composite material to provide lightweight, metal-free protection.



FIT4YOU

The patented FIT4YOU technology, with the 3 ETPU inserts included in the pack, allows the shoe's cushioning to be personalised



Customised comfort

The special pressed sheet allows you to create your own comfort by choosing from 3 different ETPU inserts included in the pack.



ESD protection

ESD certified to protect user and machinery from electrostatic charges



Certifications and Standards

CE S1PS FO SR ESD EN ISO 20345:2022



Specifications

LACING: traditional
WEIGHT (INDICATIVE SIZE 42): 550 g
TYPE: low

Lightness

- Highly breathable mesh fabric with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- Traditional lacing

Comfort

Dual-density polyurethane

Safety

3-density cushioning ETPU insert and EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules.
Durability: Composite fibre, ceramic treatment.

Coded items

	Art.	EU	UK	 mm
072700137	7270Y 37	37	4,5	251
072700138	7270Y 38	38	5	257
072700139	7270Y 39	39	6	263
072700140	7270Y 40	40	6,5	269
072700141	7270Y 41	41	7	276
072700142	7270Y 42	42	8	282
072700143	7270Y 43	43	9	290
072700144	7270Y 44	44	10	296
072700145	7270Y 45	45	10,5	304
072700146	7270Y 46	46	11	311
072700147	7270Y 47	47	12	317
072700148	7270Y 48	48	13	324

