

USB 5 Gbps Memory Stick 256 GB - Metal Housing

Description

This USB memory stick by Delock can be used to save and transport data, e.g. photos, videos or music. Due to the stylish design with **eyelet**, the small USB memory stick can be easily attached to the key ring for transport.

Small sturdy helper

Due to its small dimensions and its sturdy housing, this Delock USB stick is particularly suitable for travelling. Due to its **tiny size**, the USB stick fits into any trouser pocket.



256 GB

Item no. 54006

EAN: 4043619540068

Country of origin: China

Package: Retail Box

Technical details

- Connector:
1 x USB 5 Gbps Type-A male
- Capacity: 256 GB
- Housing material: metal
- Maximum read speed: 109 MB/s
- Maximum write speed: 68 MB/s
- Maximum write cycles: 3000
- Operating temperature: 0 °C ~ 70 °C
- Storage temperature: -25 °C ~ 85 °C
- Power consumption: max. 5 W
- Field of application: consumer
- Bootable
- Plug & Play
- Dimensions (LxWxH): ca. 21.8 x 12.1 x 4.5 mm

System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.15 or above
- Mac OS 12.4 or above
- Windows 10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB 5 Gbps memory stick

Images



Technical characteristics

Storage temperature:	-25 °C ~ 85 °C
Read:	109 MB/s
Maximum power consumption:	5 W
Maximum write cycles:	3000
Write:	68 MB/s
Memory capacity:	256 GB

Physical characteristics

Length:	21.8 mm
Width:	12.1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de