


910MQ/PE**Nasadki z końcówką trzpieniową sześciokątną****EN 60900**

	art.	mm	Ø mm	L mm	
009100604	910MQ/PE	4	24	100	70
009100605	910MQ/PE	5	24,5	100	75
009100606	910MQ/PE	6	25,0	100	76
009100608	910MQ/PE	8	25,0	100	75
009100610	910MQ/PE	10	25,5	100	80

