

Pushbutton, 18.2 mm, screw terminal, momentary contact function, 2 NO, bezel black



Description

Pushbutton with mounting hole diameter 18.2 mm, non-illuminated, 250 V / 4 A



technical data

> general

Bezel color	black
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
Net weight	16 g
Operating life	50,000 cycles
B10	65,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
Minimum order quantity (MOQ)	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Country of origin	HU

> mounting diameters

Outside dimension, length	22 mm
Outside dimension, width	22 mm
Outside dimension, height	44.5 mm
Mounting hole	18.2 mm
Mounting depth	34 mm
Installation height	10.5 mm

> mechanical data

Terminal on the rear	Screw terminal
Fixing	Threaded ring
Actuation function	momentary contact function

direct links

> [RAFI eCatalog](#)

Operating force, min.	9.5 N
Operating travel, max.	5 mm
Contact function	2 NO
Contact system	Bridge-sliding contact
Contact material	Silver

> electrical data

Rated voltage, max.	250 V
Rated current, max.	2 A