



## BETA 1221

### Morphos screwdrivers for slotted head screws



### Certifications and Standards



## Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

### HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the palm contact points, improving thrust and clamping efficiency.

### CONTROL AND PRECISION

The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

### PERFECT GRIP AND ANTI-ROLL

The embossed texture ensures a reliable grip even under the most difficult conditions. The triangular profile prevents rolling on the work surface and promotes stable and continuous use.

### STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



### TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



### CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



### ANTI-ROTATION

The triangular shape prevents rolling on the workbench, improving safety and stability.

## Dimensions



## Certifications and Standards

## Coded items

|  | Art.         | SxAxL<br>mm | L1<br>mm | Ø<br>mm | <br>g |
|-----------------------------------------------------------------------------------|--------------|-------------|----------|---------|------------------------------------------------------------------------------------------|
| 012210003                                                                         | 1221 2,5X50  | 0,4x2,5x50  | 151      | 2,5     | 35                                                                                       |
| 012210006                                                                         | 1221 2,5X75  | 0,4x2,5x75  | 176      | 2,5     | 37                                                                                       |
| 012210009                                                                         | 1221 3X75    | 0,5x3x75    | 176      | 3,0     | 39                                                                                       |
| 012210012                                                                         | 1221 3X100   | 0,5x3x100   | 201      | 3,0     | 40                                                                                       |
| 012210018                                                                         | 1221 3,5X75  | 0,6x3,5x75  | 176      | 3,5     | 41                                                                                       |
| 012210021                                                                         | 1221 3,5X100 | 0,6x3,5x100 | 201      | 3,5     | 43                                                                                       |
| 012210030                                                                         | 1221 4X100   | 0,8x4x100   | 209      | 4,0     | 64                                                                                       |
| 012210033                                                                         | 1221 4X125   | 0,8x4x125   | 234      | 4,0     | 67                                                                                       |
| 012210036                                                                         | 1221 4X150   | 0,8x4x150   | 259      | 4,0     | 70                                                                                       |
| 012210039                                                                         | 1221 5,5X100 | 1x5,5x100   | 209      | 5,0     | 72                                                                                       |
| 012210040                                                                         | 1221 5,5X125 | 1x5,5x125   | 233      | 5,0     | 76                                                                                       |
| 012210042                                                                         | 1221 5,5X150 | 1x5,5x150   | 259      | 5,0     | 79                                                                                       |
| 012210048                                                                         | 1221 6,5X100 | 1,2x6,5x100 | 221      | 6,0     | 102                                                                                      |
| 012210050                                                                         | 1221 6,5X125 | 1,2x6,5x125 | 246      | 6,0     | 109                                                                                      |
| 012210051                                                                         | 1221 6,5X150 | 1,2x6,5x150 | 271      | 6,0     | 115                                                                                      |
| 012210057                                                                         | 1221 8X150   | 1,2x8x150   | 283      | 8,0     | 168                                                                                      |
| 012210060                                                                         | 1221 8X200   | 1,2x8x200   | 333      | 8,0     | 185                                                                                      |
| 012210066                                                                         | 1221 10X200  | 1,6x10x200  | 333      | 9,5     | 230                                                                                      |
| 012210069                                                                         | 1221 12X250  | 2x12x250    | 333      | 10,0    | 276                                                                                      |

**Scan the QR Code to access the web tab**

Specs, media and documentation in one click.

