




BETA 1227TX/S13

Set of 13 Morphos screwdrivers for Torx® head screws



Certifications and Standards



Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the contact points of the palm, improving thrust and tightening efficiency.

CONTROL AND PRECISION

The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

PERFECT GRIP AND ANTI-ROLL

The embossed texture ensures a reliable grip even under the most difficult conditions. The triangular profile prevents rolling on the work surface and promotes stable and continuous use.

STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



ANTI-ROTATION

The triangular shape prevents rolling on the workbench, improving safety and stability.

Certifications and Standards



Coded items

	Art.	
012270213	1227TX/S13	T5-T6-T7-T8-T9-T10-T15 T20-T25-T27-T30-T40-T45

