

Technical Datasheet

tasker® C604 – 4x0,08 mm²

28 AWG Flat Telephone Cable



CATEGORY Flat telephone Cable (See Data Network Catalogue)

APPLICATIONS Electronics and data transmission.

- A:** PVC Sheath. Available in different colors.
Outer Dimension: 2,40x4,80 (±0,20) mm.
- B:** Cores Insulation with PPE – Diam. Ø 0,90 mm (±0,20) .
Color Code: Black, Red, Green, Yellow.
- C:** Stranded O.F.C. Red Copper formation 7x0,12 mm.
Nom. Cross section 4x0,08 mm² (28 AWG).

MARKING Cable not marked

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE**, **PUR**.

Cable Properties

Conductor Resistance	203 Ω/Km
Core Capacity	100 pF/m
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 15.02.18
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			10% measurement tolerance, unless otherwise indicated