



BETA 944MH

Deep, hi-torque Morphos hexagon nut spinners, long series



Certifications and Standards



Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

HEXAGON SOCKET LONG SERIES

The length allows work on deep elements. Reduced thickness for quick screwing even in tight spaces.

CONTROL AND PRECISION

The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the palm contact points, improving thrust and clamping efficiency.

STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



ANTI-ROTATION

The triangular shape prevents rolling on the workbench, improving safety and stability.

Dimensions



Certifications and Standards

Coded items

	Art.	mm	L mm	L1 mm	A1 mm	A mm	Ø mm
009441003	944MH 4	4	246	125	20	3,0	6,5
009441004	944MH 5	5	246	125	25	3,5	7,6
009441005	944MH 5,5	5,5	246	125	30	4,0	8,2
009441006	944MH 6	6	246	125	35	5,0	8,8
009441007	944MH 7	7	246	125	35	6,0	10
009441008	944MH 8	8	258	125	50	7,0	11,2
009441009	944MH 9	9	258	125	50	8,0	12,6
009441010	944MH 10	10	258	125	50	8,5	13,8
009441011	944MH 11	11	258	125	50	9,0	15,1
009441012	944MH 12	12	258	125	50	9,5	16,4
009441013	944MH 13	13	258	125	55	10,5	17,6
009441014	944MH 14	14	258	125	55	11,5	18,8

