

USB Type-C™ 3.2 Docking Station for 2 x 2.5" SATA HDD / SSD with Clone Function

Description

This docking station by Delock enables an external connection of up to **two 2.5" SATA HDDs or SSDs** through the **USB-C™** interface. This solution does not require an external enclosure since the drive can be plugged into the docking station directly. Furthermore the **clone function** enables to copy the content of one HDD to another without using a PC.

Good cooling

A **fan in the bottom area** of the docking station ensures sufficient cooling of the HDDs or SSDs used, so that the operation also works without problems with closed lid. Another advantage is that **the noise level of the HDDs will be reduced**.

Suitable as transport box

Due to the **elegant design** and the specially designed lid, the docking station is also suitable as a transport box for two 2.5" memories.



Item no. 63084

EAN: 4043619630844

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) USB Type-C™ female
 - 2 x SATA 6 Gb/s 22 pin receptacle
 - 1 x DC jack
- Chipset: Asmedia ASM1352R
- Function key:
 - 1 x Clone button
 - 1 x On / Off switch
- Suitable for 2.5" SATA HDD / SSD
- Suitable for all SATA HDDs up to SATA 6 Gb/s
- Data transfer rate up to 6 Gbps
- LED indicator for power, access and copy status
- Width of the slot: ca. 12.5 mm
- Dimensions (LxWxH) incl. lid: ca. 132 x 93 x 93 mm
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.6 A
- Output: 5 V / 3 A
- Ground outside, plus inside
- Dimensions:
inside: ø ca. 1.35 mm
outside: ø ca. 3.5 mm
length: ca. 10 mm

System requirements

- Android 9.0 or above
- Chrome OS 76.0 or above
- iPad Pro (2018)
- Linux Kernel 3.12 or above
- Mac OS 10.15.2 or above
- Windows 8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-C™ port

Package content

- Docking station
- Cable USB-C™ male to USB-C™ male, length ca. 1 m
- External power supply 5 V / 3 A (incl. EU, UK and USA plug)
- User manual

Images



General

Function:	Plug & Play
Suitable for data medium:	2.5" SSD or HDD
Supported operating system:	Android 9.0 or above Chrome OS 76.0 or above Linux Kernel 3.12 or above Mac OS 10.15.2 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

Interface

External:	1 x DC jack 1 x USB 10 Gbps USB Type-C™ female
Internal:	2 x SATA 22 Pin Buchse

Technical characteristics

Chipset:	Asmedia ASM1352R
----------	------------------

Physical characteristics

Housing material:	Plastic
Cable length:	1 m
Length:	132 mm
Width:	93 mm
Height:	93 mm
Colour:	white

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de