
LED tape K-BTRGB30-1510-24, 3000K, 330 lm/m, 15.1 W/m, IP20

Ref. K-BTRGB30-1510-24



Dimensions: Width [W]: 12 mm | Height [H]: 2.5 mm | Cut every [C]: 125 mm | LED spacing [D]: 20.83 mm

CRI 90+ | IP20 | 24 V

TECHNICAL SPECIFICATIONS

IP protection rating	20
LED color	RGB+W
CRI	90
Color temperature	3000 K RED GREEN BLUE
Lumen output	330 lm/m 130 lm/m 245 lm/m 55 lm/m
Efficiency	22 lm/W 26 lm/W 49 lm/W 11 lm/W
LxBy	L80B50
Lifetime	100000 h
Possibility of bending	yes
Input voltage	24 V DC
Power consumption	15.1 W/m
Beam angle	120°
MacAdam's ellipse	3 SDCM
Number of LEDs per 1 m	48
Number of LEDs per cut section	6 pcs
DimensionsxWxH	12 mm x 2.5 mm

- UL Listed
- CRI 90+
- Possibility of bending in the light plane