

Eaton 35NHG000B

Catalog Number: 35NHG000B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 35A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Metal plated copper contact plate, Ceramic body

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	35NHG000B
Packing Unit	
Case Pack	
Pack	
Quantity	
60	
3	
Length	
420 mm	
83 mm	
Height	
140 mm	
56 mm	
ERP Name	
SAP-UNITY	
SAP-UNITY	
Product Height	
51 mm	
Product Weight	
131 g	

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	35NHG000B
Packing Unit	
Case Pack	
Pack	
Quantity	
60	
3	
Length	
420 mm	
83 mm	
Height	
140 mm	
56 mm	
ERP Name	
SAP-UNITY	
SAP-UNITY	
Product Height	
51 mm	
Product Weight	
131 g	



Compliances

RoHS Compliant

Certifications

IEC 60269-1

Electrical data

Amperage Rating

35 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

DIN 43620

Fuse size

NH000

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia