

USB Type-C™ Docking Station 4K - HDMI / USB / Gigabit LAN / PD 3.0 90 W with switches

Description

This docking station by Delock can be connected to a computer with a **USB-C™ DP Alt Mode or Thunderbolt™ 3 or Thunderbolt™ 4 port** and provides a variety of interfaces. A monitor can be operated at the **HDMI** output port by a maximum resolution up to **4K**. **Two built-in USB Type-A and one USB-C™ port** allow the use of peripherals.

Integrated 10/100/1000 Mbps LAN interface

In addition, the docking station with integrated **RJ45 Gigabit LAN** connection expands a PC or laptop by a network interface.

USB Power Delivery (USB PD 3.0) support up to 90 watt

The docking station has a USB Type-C™ Power Delivery port. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to **90 watts** during operation.

Switches for each port

The Delock docking station has **switches for each port** on the top. This allows each port to be switched on or off individually, which is indicated by an **LED on the switch**. This can be useful in a meeting, for example, if you want to disconnect the monitor from the connected laptop for a short time.



Item no. 92000

EAN: 4043619920006

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 2 x USB 5 Gbps Type-A female
 - 1 x USB 5 Gbps USB Type-C™ female
 - 1 x HDMI female
 - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
 - 1 x USB Type-C™ PD female (power supply)
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports HDCP 1.4 and 2.2
- Supports HDR
- Input power PD port: 100 W, 10 W are used for the docking station

- Output power for host: max. 90 W
- 6 x LED indicator
- 6 x switch
- Metal housing
- Cable length without connectors: ca. 28 cm
- Colour: midnight blue
- Dimensions (LxWxH): ca. 139 x 50 x 17 mm

System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 14.2.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 7
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- USB-C™ docking station
- User manual

Images



General

Function:	HDR / HDR10 mirror and extend
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 6.2 or above Android 14.0 or above Mac OS 14.2.1 or above
LED indicator:	6 x

Interface

Output:	1 x RJ45 jack 1 x USB Type-C™ female (power supply) 1 x USB 5 Gbps USB Type-C™ female 1 x HDMI-A female 2 x USB 5 Gbps Type-A female
Input:	1 x USB Type-C™ male

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	metal
Cable length:	28 cm
Length:	139 mm
Width:	50 mm
Height:	17 mm
Colour:	midnight blue

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de