


PUSH SWITCH MODEL PS6 SERIES





RATING: 6A 125/250V~ μ10T85/55(cURus/ENEC15)

3A 48VDC μ10T85/55(cURus/ENEC15)

INSULATION RESISTANCE:100MΩ (MIN), DC 500V

DIELECTRIC STRENGTH:500VAC FOR 1 MINUTE

CONTACT RESISTANCE : 20m Ω INITIAL (MAX).



MOUNTING HOLE

NOTE:TOLERANCES UNLESS OTHERWISE SPECIFIED:± .012/0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	DWG NO
4			DRAWN BY	達志各	DESIGNED BY	蔡劍	SCALE	2/1	PS6 SPEC DRAWING	S9598C
2025.04.22	整理圖面，重新出圖	達志各	CHECKED BY		APPROVED BY		DATE	2023.12.11	PS6-11BBA-C1	
2024.12.12	增加安規	達志各								
2023.12.11	首次出圖	達志各								