
S/FTP Cat. 6A LSZH patch cord, purple, 0.25 m

PP6A-LSZHCU-V-0.25M



- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated contacts

Specifications

Category: category 6A
Type: SSTP (dual shielded)
Frequency bandwidth: Max. 500 MHz
Compliance with ANSI / TIA / EIA-568B standards
Conductor: AWG 27 (7 x 0.135 mm wire), CU
Conductor insulation: FM-PE 1.0 mm
Shielding: AL foil + braid shield (16 x 4/0.12 mm)
LDPE filler: yes
Polyester tape: yes
Drain wire: n/a
Jacket material: LSZH
Jacket braiding: n/a
Jacket outer diameter: 6.2 mm
Length: conform item description
Color: conform item description

Features

- Patch cord with foil shielded pairs and braided cable, CAT 6A

- Gold plated contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

Packaging

Q'ty in crtn, pcs	500
Crtn volume, CUM	0.041
Crtn weight, kgs	10.5
Individual package size LxWxH:	130x10x175 mm
Carton size LxWxH:	400x300x340 mm
Country of origin	CN
Barcode	8716309091374
Customs code	8544421000

Certificates

Copyright © 2009–2022, Gembird Software Ltd.

Wittevrouwen 56 | 1358CD Almere | The Netherlands | Phone: +31-36-5211588 | www.cablexpert.com | postmaster@cablexpert.com