Type BLR-I-912-G
Fuse Block - Indicating
12 Pole - Regular, ATC/ATO Auto Blade
With 12-Position Grounding Block

www.optifuse.com (619) 593-5050


Specifications:

Max Voltage: 32VDC
Max Current Rating: 30A per Circuit - 100A Max
Fuse Type: Regular, ATO / ATC, Auto Blade (APR / ANR series)
(Fuses or Circuit Breakers)
Mounting: 4 mounting holes, 4.5mm diameter
Indicating LED – Red
Temperature Rating: -20° C ~ +85° C

Material:

Housing & Base: PBT, Black
Cover: PC, Clear
Terminals: Copper

Mechanical Dimensions: Inches [mm]



Warning:	-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame. -Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.