
mm [inch]





ST1020 TA05 M

Minimum centers:	2.54 [.100]
Full travel:	5.30 [.209]
Working travel:	4.00 [.157]
Current rating:	5-8 A
Probe resistance:	< 20 mΩ
Operating Temperature:	-30°C up to +120°C
Plunger material:	BeCu/ Gold Plated
Barrel material:	Brass / Gold Plated
Spring material:	Music wire / Gold Plated

Spring force at working stroke: 1.5 N [5.4 oz]

© COPYRIGHT 2017
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	Cs.V.	05.12.2017.
Drawed		
Checked		
Note		

Catalog Item: **ST1020 TA05 M**

Drawing No.:

A4 SHEET 1 OF 1

EQUIP TEST
TEST – SUPPORT – INNOVATE