

USB Type-C™ 3.1 Docking Station HDMI 4K 30 Hz + VGA + LAN + USB PD

Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3 port and provides a variety of interfaces. One monitor can be operated at the HDMI or VGA output. One built-in USB Type-A port allows the use of peripherals. With a USB-C™ power supply, laptops such as the MacBook or Chromebook can be charged during operation.



Item no. 87731

EAN: 4043619877317

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - front side:
 - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
 - 1 x HDMI-A 19 pin female
 - 1 x VGA 15 pin female
 - 1 x USB 3.0 Type-A female
 - back side:
 - 1 x USB Type-C™ female (power supply)
 - 1 x USB Type-C™ male
- Resolution:
 - HDMI up to 2560 x 1440 @ 60 Hz / 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
 - VGA up to 1920 x 1080 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Only 1 monitor usable with the adapter
- Output power USB Type-A female: max. 4.5 W
- Input power PD: max. 100 W
- Operating temperature: 0 °C ~ 45 °C
- Storage temperature: -10 °C ~ 70 °C
- Cable length incl. connector: ca. 14 cm
- Colour: white
- Dimensions (LxWxH): ca. 103 x 52 x 16 mm

System requirements

- Android 8.0 or above
- Linux Kernel 4.6 or above
- Mac OS 10.9 or above
- Windows 8.1/8.1-64/10/10-64
- Windows 10 Mobile
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ docking station
- User manual

Images



General

Supported operating system:	Android 8.0 or above Linux Kernel 4.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 8.1 32-Bit Windows 8.1 64-Bit
-----------------------------	--

Interface

Output:	1 x RJ45 jack 1 x VGA 15 pin female 1 x USB Type-C™ female (power supply) 1 x USB 5 Gbps Type-A female 1 x HDMI-A female
Input:	1 x USB Type-C™ male

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz 2560 x 1440 @ 60 Hz 1920 x 1080 @ 60 Hz
----------------------------	---

Physical characteristics

Colour:	white
---------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de