

Cable Connector RJ45 jack to RJ45 jack Cat.6A with housing and protective cap waterproof

Description

This cable connector by Delock can be used to connect or extend two RJ45 network cables and is ideal for outdoor use e.g. in the garden. With this RJ45 coupler there is a waterproof cable entry on one side with housing and screw cap, which is protected with a silicone sealing ring and the other side can be closed with the protective cap.



IP68 dust and waterproof

The coupler offers increased protection against dirt and moisture for the connection of the network cables.

Item no. 86701

EAN: 4043619867011

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 jack >
 - 1 x RJ45 jack
- 1:1 connected
- Cat.6A specification
- Shielded (STP)
- Silicone sealing ring blue
- Cap
- Protection class: IP68
- For cable diameter from 5.0 - 7.5 mm
- Operating temperature: -40 °C ~ 85 °C
- Material: plastic
- Colour: black
- Dimensions (LxWxH): ca. 74 x 29 x 29 mm

Package content

- Cable connector

Images



General

Specification:	Cat. 6A
Protection class:	IP68
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 jack
Connector 2:	1 x RJ45 jack

Technical characteristics

Operating temperature:	-40 °C ~ 85 °C
------------------------	----------------

Physical characteristics

Material:	Plastic
Shielding:	STP
Length:	74 mm
Width:	29 mm
Height:	29 mm
Colour:	black
Cable diameter:	5.0 - 7.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

