

USB 3 in 1 Retractable Charging Cable for Micro USB / 2 x USB Type-C™ with Fast Charging black

Opis

This practical 3 in 1 retractable cable by Delock can be connected to a power source with USB-A connection and can be used to charge single devices with Micro USB or USB Type-C™ interface.

Useful companion

This cable is the ideal companion for on the go e.g. on business trips or on holidays, since it combines the two most common interfaces in one cable for the latest mobile devices. This avoids annoying cable clutter and unnecessary carrying around of countless cables.

Fast charging and power

One of the two USB Type-C™ ports enables the data transfer as well as **fast charging** with a powerbank or modern USB chargers.

The other two connectors can be used for charging only.

Flexible

The charging cable can be pulled out in five stages and thus offers different cable lengths, depending on requirements.



Numer artykułu 85359

EAN: 4043619853595

Kraj pochodzenia: China

Opakowanie: Torba na zamek błyskawiczny

Szczegóły techniczne

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB Type Micro-B male (only charging)
 - 1 x USB Type-C™ male (only charging)
 - 1 x USB Type-C™ male (Fast Charging + data transfer)
- Supports only charging function
- Maximum output current: 3 A
- Voltage: max. 5 V
- Fast Charging function: 10 V / 2.4 A
- Data transfer rate up to 480 Mb/s
- Cable gauge: 22 AWG
- Contacts gold-plated
- Colour: black / green / blue
- Length incl. connectors: ca. 113 cm (total incl. housing)
 - retracted:
 - USB-A Host-cable ca. 2.5 cm

3 Device-cable ca. 14.5 cm
extended:
USB-A Host-cable ca. 45 cm
3 Device-cable ca. 59 cm

Wymagania systemowe

- Power source with a free USB Type-A port
- PC or laptop with a free USB Type-A port

Zawartość opakowania

- Cable

Zdjęcia



Ogólne

Styl:	Płaski przewód
-------	----------------

Interfejs

Złącze 1:	1 x USB 2.0 Typ-A męski
Złącze 2:	1 x USB 2.0 Typ Micro-B męski 2 x USB 2.0 Type-C™ męski

Właściwości techniczne

Szybkość transmisji danych:	480 Mbps
Maksymalny prąd:	2,4 A 3 A
Napięcie:	5 V 10 V

Właściwości fizyczne

Wykończenie złącza:	pozlacane
Średnica kabla:	22 AWG
Długość:	1,13 m
Kolor:	niebieski zielony czarny

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de