



Qoltec RG58 Coaxial Cable | N Female | RP-SMA Male | 1m

Product code: 57030

Interference resistant Qoltec coaxial cable with a length of 1m.
Designed for the construction of indoor and outdoor individual or collective antenna installations.

Don't lose your signal

Choosing the right coaxial cable is extremely important as it picks up the signal from the antenna and sends it to your TV or DVB-T receiver.

It is used for advanced installations in closed-circuit television systems, for the installation of antennas, for cable television reception or for home audio-video connections. Even the most modern TV set and antenna set will not provide maximum image quality, when the cable is of poor quality, additionally, repeated signal fading will become a nuisance - we have a solution in the form of Qoltec coaxial cable.

With attention to every detail

When choosing a coaxial cable, an important element is durable insulation, which protects the cable against weather conditions, water, UV rays and possible mechanical damage. The presented model is resistant to the above-mentioned factors and ensures a long service life.

TRUST CONFIRMED BY WARRANTY

Do you care about the high quality of the product you buy? Our solutions will meet your expectations. Each of the coaxial cables we offer is covered by a 24-month warranty valid from the date of purchase.

Technical data

Producer	Qoltec
Cable length	1 m
Guide material	CCA
Type of fiber	AP+AA
Connector type	N female / RP-SMA male
Type of wire	RG58
Insulation material	PE
Impedance	50
Colour	Black
Package contents	Qoltec Coaxial cable
Package depth / length [mm]	30
Package width [mm]	80
Package height [mm]	210
Net weight	0,0400 kg
Gross weight	0,0450 kg
Warranty	24 months
EAN code	5901878570303