


1668A
Kątowniki powierzchniowe ze stopką, ze stali normalizowanej
DIN 875/2

	art.	L mm	L1 mm	B mm	C mm	H mm	S mm	ī g
016680110	1668A 100	100	70	19,4	5,5	19,3	5,0	155
016680115	1668A 150	150	100	24,5	5,5	25,0	5,0	330
016680120	1668A 200	200	130	29,5	5,5	30,1	5,0	525
016680125	1668A 250	250	165	34,5	7,0	34,1	7,0	1025
016680130	1668A 300	300	176	34,5	7,5	34,5	7,5	1200

