DIGITUS® CK10, wired keyboard, German layout (QWERTZ), 105 keys

DA-20167

EAN 4016032511045



Office Keyboard Corded GER black 1,8 m USB cable

This wired keyboard with a German QWERTZ layout offers quiet, precise typing and a slim, ergonomic design. The full 105-key layout, including a numeric keypad and all important special characters and umlauts, enables intuitive typing and efficient work in German-speaking office, government agency, and home office environments. The comfortable “whisper keys” provide a pleasantly quiet typing experience and support focused work—even at shared workstations. Thanks to its slim profile, medium-height keys with a slight concave shape, and practical height adjustment via fold-out feet, the keyboard can be comfortably adapted to your personal working style. Laser-etched key symbols ensure lasting legibility, even with frequent use. The wired USB-A connection provides stable, lag-free input without the need for batteries or wireless interruptions. Thanks to Plug & Play, the keyboard is ready to use immediately—simply connect it via USB and get started right away. With a 1.8 m cable length, a non-slip design, and a weight of 525 g, it also offers flexible placement and a secure grip on your desk. Three status LEDs for Caps Lock, Num Lock, and Scroll Lock round out its practical features.

The keyboard combines quiet, precise typing comfort with a slim, ergonomic, and timeless design

- Keyboard Layout: QWERTZ
- Keyboard layout: German
- Number of keys: 105
- USB port: USB 2.0
- Cable length: 1.8 m
- Tilt adjustment with rubberized feet
- Tilt angle: 2° (folded), 7° (unfolded)
- 3 status LEDs (Caps Lock, Num Lock, and Scroll Lock keys)
- Switch Type: High-Quality Membrane Technology
- Sound level: 42.5 ± 10 dB
- Key travel: 2.8 ± 0.2 mm
- Actuation force: 55 ±10 N (standard keys), 70 ±10 N (Enter and Spacebar)
- Abrasion-Resistant Laser Marking
- Character height: 4.4 mm (letters), 3.4 mm (numbers)
- Distance from key center to key center: 19 mm
- Service life: 10 million keystrokes per key
- MTBF: >100,000 hours
- Gloss level: Matte; 3.8–6.4 GU
- Current consumption: 50 mA
- Supply voltage: 5V (DC)
- Operating temperature: 0–40°C
- Storage temperature: -40 to 55° C
- Weight: 525 g
- Dimensions: 452 x 159 x 24 mm
- Color: Black
- System Requirements: Windows 7, 10, 11, USB-A port


Package contents

- 1 keyboard
- 1 user manual

Logistics


	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	10	8.00	30.30	49.50	22.80	34,196.60
Packaging Unit Inside	1	0.80	0.00	0.00	0.00	0.00
Packaging Unit Single	1	0.80	20.20	48.20	2.70	2,628.83
Net single without Packaging	1	0.80	20.20	48.20	2.70	2,628.83

More images:











Safety notes

- Do not open, modify, or repair the device yourself.
- Keep the device and its power cord out of the reach of small children to prevent the cord from wrapping around their neck or body and posing a strangulation hazard.
- Lay the power cord away from walkways and in such a way that no one can get caught on it, to prevent tripping and falling injuries.
- During prolonged use, be sure to maintain an ergonomic posture for your body, hands, and arms, and take regular breaks to avoid discomfort caused by repetitive or prolonged strain.
- Do not continue to use the device if the power cord, plug, or housing shows visible damage, to prevent malfunctions or damage to the connected device.
- Protect the connection cable from being crushed, severely kinked, or subjected to excessive tension to prevent damage and resulting malfunctions.
- Use and store the device only within the operating conditions specified by the manufacturer to prevent damage to the device and impairment of its functionality.
- When cleaning, follow the manufacturer's instructions and disconnect the device from the computer before cleaning.
- Do not use harsh cleaning agents, solvents, or abrasive cleaners.
- Never spray the device directly with water or cleaning sprays
- Battery and Rechargeable Battery Safety (for wireless keyboards and mice)
- Never throw batteries into a fire, open them, or short-circuit them. Risk of explosion and fire.
- Keep batteries out of the reach of children. Swallowing batteries can be life-threatening.
- Remove dead batteries from the device immediately to prevent damage caused by leakage.
- Electronic devices and batteries must not be disposed of with household trash. Please follow local disposal regulations and use the designated collection systems for used electronic devices.

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
https://www.assmann.com
info@assmann.com