



## BETA 7276N FitEVOLUTION microfibre ankle shoe, water-repellent



### Certifications and Standards

CE S3S FO SR ESD EN ISO 20345:2022

## Features

The 7276N is the perfect synthesis of durability and functionality: BETA orange outsole and details enhance the robust black microfibres upper.

### FIT4YOU system

Create your own comfort with BETA's patented FIT4YOU system: a special cavity in the penetration proof insole allows you to replace the ETPU insole at any time, choosing from three different densities included in the pack.

### ETPU inserts

ETPU is known for its excellent anti-shock and shock-absorbing properties. The three inserts soft, intermediate and rigid make it easy and immediate to customise the softness and support of the shoe to suit your needs.

### All-season durability

The water-repellent microfibres upper is incredibly resistant to stains and scratches, perfect for all-season use. It is ideal for shoes built to last, without compromising on quality.

### Metal-free

Composite toe cap and midsole are made of composite material to provide lightweight, metal-free protection.



**FIT4YOU**  
The patented FIT4YOU technology, with the 3 ETPU inserts included in the pack, allows the shoe's cushioning to be personalised



**Customised comfort**  
The special pressed sheet allows you to create your own comfort by choosing from 3 different ETPU inserts included in the pack.



**ESD protection**  
ESD certified to protect user and machinery from electrostatic charges



## Certifications and Standards

CE S3S FO SR ESD EN ISO 20345:2022



## Specifications

LACING: traditional  
 WEIGHT (INDICATIVE SIZE 42): 650 g  
 TYPE: high

### Lightness

- Water-repellent microfibre
- Heel stability support
- Traditional lacing

### Comfort

Dual-density polyurethane

### Safety



3-density cushioning ETPU insert and EVA FOAM underfoot cover

### Protections

Tip: Polymer material, 200 joules.

Durability: Composite fibre, ceramic treatment.

## Coded items

	Art.	EU	UK	 mm
072760237	7276N 37	37	4,5	251
072760238	7276N 38	38	5	257
072760239	7276N 39	39	6	263
072760240	7276N 40	40	6,5	269
072760241	7276N 41	41	7	276
072760242	7276N 42	42	8	282
072760243	7276N 43	43	9	290
072760244	7276N 44	44	10	296
072760245	7276N 45	45	10,5	304
072760246	7276N 46	46	11	311
072760247	7276N 47	47	12	317
072760248	7276N 48	48	13	324

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

