
Delock Junction Box for network cable Cat.6 UTP LSA toolless

Description

With this coupler from Delock you can extend or repair two network cables without additional connectors. The LSA blocks can be used with a punch down tool; alternatively, a tool-free connection is possible.



Item no. 86167

EAN: 4043619861675

Country of origin: Taiwan, Republic of China

Package: Zip poly bag

Technical details

- Connectors: LSA block > LSA block (toolless)
- Unshielded (Cat.6)
- TIA-568A/B pinout
- Cable diameter up to 0.644 mm (22 – 26 AWG)
- Dimensions (LxWxH): ca. 48 x 25.8 x 24.7 mm

Package content

- Junction Box
- 2 zip-ties
- Adhesive pad, 45 x 25 mm

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Suitable for conductor gauge:	22 - 26 AWG

Interface

Internal:	2 x LSA block

Technical characteristics

Category:	Cat.6A

Physical characteristics

Housing colour:	white
Housing material:	Plastic
Shielding:	unshielded
Length:	48.0 mm
Width:	25.8 mm
Height:	24.7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**