

PRODUCT-DETAILS

TC5142

SADDLE SPRT BASE NAT NYL SCREW MNT



General Information

Extended Product Type	TC5142
Product ID	7TAG009870R0003
EAN	5414363058830
Catalog Description	SADDLE SPRT BASE NAT NYL SCREW MNT
Long Description	Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, 100 Pack

Ordering

EAN	5414363058830
UPC	786210873589
Country of Origin	United Kingdom (GB) United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	500 piece
Package Level 2 Width	9.2 in 234 mm
Package Level 2 Height	5.1 in 130 mm
Package Level 2 Depth / Length	9.4 in 239 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19750903
Material	Nylon/Polyamide 6.6
Mounting Holes	#10
Mounting Type	Screw
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Saddle Support Base
Special Functions	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5142
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC5142
REACH Declaration	9AKK107992A3992
RoHS Information	9AKK107992A8809

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

