



Flexible strain relief for cables
model : R3.0/23-WH

Dimmension	
Cable cross section (A)	3.0 mm
Total length (F)	23mm
Working length (E)	18.8mm
Width (B)	8.4mm
Width (D)	8.4mm
Mounting hole (C)	Max 5.6 x 5.6mm
Maximum mounting wall thickness (G)	2.5mm
Other	
Material	Hydrogenated styrene butadiene block copolymer (SEBS)
	Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)
	Ethylene Propylene Diene Monomer (EPDM)
	Styrene butadiene styrene block copolymer (SBS)

