




Pliable protective conduit system ICTA range, made of PP: classification 3422, available in seven diameters, from 16 to 63 mm, with or without cable puller and in four different colour to allow the identification of the various electrical lines. Suitable for electrical system and/or data transmission. Suitable for flush-mounting installation in concrete, plasterboard walls and floating floors. Certified Halogen Free in compliance with EN 60754-2 and suitable for hollow walls for instance in public areas (theatres, schools and cinemas...). The pallets of ICTA conduits are packed in white stretch film to prevent direct exposure of the products to UV rays and greater weather resistance.

|                                                              |                                                |                                                                 |                                                                                      |
|--------------------------------------------------------------|------------------------------------------------|-----------------------------------------------------------------|--------------------------------------------------------------------------------------|
| Colour                                                       | Dark grey                                      | Material                                                        | PP self-extinguishing                                                                |
| Type                                                         | with cable puller                              | Conduits Ø (mm)                                                 | 40                                                                                   |
| Glow Wire Test                                               | 850 °C                                         | Type of material                                                | Halogen free in compliance with EN 60754-2 e Low smoke in compliance with EN 61034-2 |
| Electrocod                                                   | 2111                                           | Resistance to compression                                       | 3 (Medium - 750 N)                                                                   |
| Resistance to impact                                         | 4 (Heavy - 6 J)                                | Resistance to bending                                           | 3 (Pliable - self recovering)                                                        |
| Electrical characteristics                                   | 2 (With electrical insulating characteristics) | Protection against ingress of solid objects without accessories | 0                                                                                    |
| Protection against ingress of water                          | 0                                              | Resistance against corrosion                                    | PP naturally resistant to corrosion                                                  |
| Fire resistance                                              | 1 (Non-flame propagating)                      | Insulation resistance                                           | 100 MΩ a 500V for 1 minute                                                           |
| Protection against ingress of solid objects with GF coupling | 4                                              | Dielectric rigidity                                             | 2000 V a 50 Hz for 15 minutes                                                        |
| Standard                                                     | EN 61386-1 EN 61386-22                         | Classification                                                  | 3422                                                                                 |

### DIMENSIONAL



### TECHNICAL SYMBOLOGY

**GWT**

850 °C



EN 61034-2  
EN 60754-2



### STANDARDS/APPROVALS



GEWISS S.p.A. Via A. Volta, 1  
24069 Cenate Sotto - Bergamo - Italy  
tel. +39 035 94 61 11 fax +39 035 94 69 09  
Company subject to the management and  
coordination of Polifin S.p.A.

www.gewiss.com  
sat@gewiss.com  
Last update 23/01/2026

Data, measures, designs and pictures are shown  
only as informative purposes,  
and could be changed without previous notice