




Continuous Rating	200Amps 32VDC Max.	Mounting Hole	Circuit Diagram	
Intermittent Rating	300 Amps		OFF	ON
Cranking Rating	1000 Amps 5 sec.			
Contact Resistance	50m ohm Max			
Insulation Resistance	DC 500V 100M ohm Min			
Dielectric Strength	AC 1000V 1 minute, DC 2000V 1 minute			
Operation Temperature	-30°C~+60°C			
Switch Function	2P SPST OFF-ON			


Actuator can be taken out



***MATERIAL:**

Housing: Black, PA#66+33%GF
with White hot stamping
Actuator: Red, PBT+15%GF
Name Plate: White, ABS
with Black hot stamping
Bottom: Black, PBT+15%GF
Nut: Steel
Bolt: Brass
Hex Nut: Ni-plated, Brass
1 NUT ASSY

*Ingress Protection: IP56



For ED036 only

tolerances Unless otherwise specified ± 0.3

3/23/'21	林明呈	機種標示更新，原鑄機種A23-8修改為鑄機種A23-8BO(ECR#RAD20210303-095)					△
Date	Name	Descriptions					NO
Drawn	Checked	Approved	SCI BOM No.	1340115	Model Name	Battery SWITCH	
林明呈	許庭禎	余敏明	Customer No.		Model No.	A23-8BO	REV.
3/23/'21	2021/04/01	2021/04/01	Unit	mm	Shin Chin Industrial Co., Ltd.		1