



578E

Product no.: 578E

Tip cutter with angle at 60° for delicate work only



Widely relieved on top and bottom for better visibility



source images

The Perfect Cut - Strong, sharp and precise, every time

Weller Erem™ Cutters are designed to be strong, durable and sharp, having the highest precision available. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Cutters are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

Type		Type of Cut	Cutting Capacity
Series 500 Medium			mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0 Inch .001 .003 .007 .011 .015 .019 .023 .027 .031 .035 .039 .043 .047 .051 .055 .059 .062 .066 .070 .074 .078
	512N	Semi Flush	
	512E	Semi Flush	
	599T	Semi Flush / Carbide	
	522N	Flush	
	599E	Flush	
	532N	Super Full Flush	
	576TX1	Flush / Carbide	
	503E	Flush	
	503ETST 30°	Flush / Carbide	
	504AE	Flush	
	555E 35°	Flush	
	572E 40°	Flush	
	582E 45°	Flush	
	593AE 30°	Flush	
	575E 45°	Flush	
	592E	Flush	
	792E	Super Full Flush	
	576TX	Flush / Carbide	
	570E	Flush	
	573E	Flush	 for vertical tip cutting





Technical Data

Length mm	110
Length of cutting edges mm	8
Head width mm	11
Head thickness mm	6
Head length mm	0.819
Max. cutting capability – hard wire mm	---
Weight in oz	2.363
Length of cutting edges Inches	0.315
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	20.8
ESD-safe	---
Cut	---
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	1
Length inches	4.331
Weight in g	67
Erem applications	---