

USB Type-C™ Docking Station for Mobile Devices 4K - HDMI / Hub / LAN / PD 3.0 with LED illumination

Description

This docking station by Delock can be connected to a mobile device with a USB-C™ DP Alt Mode or Thunderbolt™ 3 port and provides a variety of interfaces. One monitor can be operated at the **HDMI** output. Three built-in **USB** ports allow the use of peripherals. The **gigabit network** port enables the connection to the network.

USB Power Delivery (USB PD 3.0) support up to 87 watt

The docking station has a **USB Type-C™ Power Delivery port** to connect the power supply of the laptop or tablet to charge it. In addition it also supplies the USB ports with power. The docking station can also be used without a power supply.

LED design illumination

As soon as the docking station is connected via the USB-C™ plug, an **LED** at the bottom edge lights up in a unique design.

Small sturdy helper

Due to its **small dimensions** and its **sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 87742

EAN: 4043619877423

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 3 x USB 3.0 Type-A female
 - 1 x HDMI-A female
 - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
 - 1 x USB Type-C™ female (power supply)
- Resolution up to 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Input power: 1 x USB Type-C™ female max. 87 W
- Metal housing
- LED illumination

- Cable length without connectors: ca. 20 cm
- Colour: grey
- Dimensions (LxWxH): ca. 75 x 75 x 19 mm

System requirements

- Android 8.0 or above
- Chrome OS 71.0 or above
- Linux Kernel 4.9.4 or above
- Mac OS 10.12 or above
- Windows 8.1/8.1-64/10/10-64/11
- Windows 10 Mobile
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

Package content

- USB-C™ docking station
- User manual

Images



General

Supported operating system:	Android 8.0 or above Chrome OS 71.0 or above Linux Kernel 4.9.4 or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 8.1 32-Bit Windows 8.1 64-Bit
-----------------------------	--

Interface

Connector 1:	1 x USB 2.0 Type-C male
Connector 2:	3 x USB 5 Gbps Type-A female
Connector 3:	1 x HDMI-A female
Connector 4:	1 x Gigabit LAN RJ45 jack 1 x USB Type-C™ Power Delivery female

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	metal
Cable length:	20 cm (without connector)
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de