

# USB Type-C™ Docking Station 4K - Dual HDMI MST / USB / Gigabit LAN / PD 3.0 85 W

## Description

This docking station by Delock can be connected to a computer with a **USB-C™ DP Alt Mode or Thunderbolt™ 3 or Thunderbolt™ 4** port and provides a variety of interfaces. Two monitors can be operated simultaneously at the **HDMI** output ports. **Three built-in USB Type-A and one USB-C™** port allow the use of peripherals.

### Multi-Stream Transport (MST)

The product is a Multi-Stream Transport (MST) hub and supports the **extended desktop configuration** of DisplayPort. In Windows, the connected monitors are controlled individually, and can be combined into one large display.

### Integrated 10/100/1000 Mbps LAN interface

In addition, the docking station with integrated **RJ45 Gigabit LAN** connection expands a PC or laptop by a network interface.

### USB Power Delivery (USB PD 3.0) support up to 85 watt

The docking station has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 85 watts during operation.



**Item no. 88271**

EAN: 4043619882717

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ female
  - 2 x HDMI-A female
  - 2 x USB 5 Gbps Type-A female
  - 1 x USB 5 Gbps USB Type-C™ female
  - 1 x USB 2.0 Type-A female
  - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
  - 1 x USB Type-C™ PD female (power supply)
- Maximum resolution (depending on the system and the connected hardware):
  - Single display: up to 3840 x 2160 @ 60 Hz
  - Dual display: up to 3840 x 2160 @ 60 Hz
- Functions: Mirrored or Extended (Windows only)
- Transmission of audio and video signals
- Supports HDCP 1.4 and 2.2
- Supports HDR

- Input power PD port: 100 W, 15 W are used for the docking station
- Output power for host: max. 85 W
- Housing material: metal / plastic
- LED indicator
- Colour: black
- Dimensions (LxWxH): ca. 125 x 62 x 19 mm

---

## System requirements

- Android 13.0 or above
- Chrome OS
- Linux Kernel 5.15 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

---

## Package content

- USB-C™ docking station
- Cable USB-C™ male to USB-C™ male, length ca. 1 m
- User manual

---

## Images



## General

|                             |   |
|-----------------------------|---|
| Supported operating system: | Chrome OS<br>Surface Pro 7<br>Windows 10 32-Bit<br>Windows 10 64-Bit<br>iPad Pro (3rd Generation) or above<br>iPad Air (4th Generation) or above<br>Windows 11<br>Linux Kernel 5.15 or above<br>Mac OS 13.1 or above<br>Android 13.0 or above |
|-----------------------------|---|

## Technical characteristics

|                            |                     |
|----------------------------|---------------------|
| Maximum screen resolution: | 3840 x 2160 @ 60 Hz |
|----------------------------|---------------------|

## Physical characteristics

|               |                           |
|---------------|---------------------------|
| Cable length: | 20 cm (without connector) |
| Length:       | 125 mm                    |
| Width:        | 62 mm                     |
| Height:       | 19 mm                     |
| Colour:       | grey<br>black             |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |