

USB Type-A Network Adapter Gigabit LAN 2 x RJ45

Description

The USB adapter by Delock offers **2 network ports** with a data transfer rate up to **1 Gbps**. Each port can be configured independently of the other, so one PC can be connected to different networks at the same time.



Item no. 64194

EAN: 4043619641949

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-A male
 - 2 x Gigabit LAN RJ45 jack
- Chipset: Realtek RTL8153
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.3x full duplex flow control
- Supports 9k Jumbo Frames
- Downwards compatible to USB 2.0
- LED indicator for power and activity
- USB bus powered
- Colour: black
- Cable length without connectors: ca. 20 cm
- Dimensions (LxWxH): ca. 84 x 35 x 17 mm

System requirements

- Linux Kernel 4.10 or above
- Mac OS 10.10 or above
- Windows 10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB Type-A Gigabit LAN adapter
- User manual

Images



General

Specification:	USB 5 Gbps
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Connector 1:	1 x USB 5 Gbps Type-A male
Connector 2:	2 x Gigabit LAN RJ45 jack

Technical characteristics

Chipset:	Realtek RTL8153
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1 Gbps

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de