

USB Type-B Network Adapter Gigabit LAN 4 x RJ45

Description

The USB 5 Gbps adapter by Delock offers four network ports with a data transfer rate up to 1000 Mbps. Each port can be configured independently of the others, so one PC can be connected to different networks at the same time.



Item no. 62966

EAN: 4043619629664

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 4 x Gigabit LAN RJ45 jack
 - 1 x 5 V DC jack 5.5 x 2.1 mm
- Chipset: Realtek RTL8153
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
- Supports IEEE 802.3x full duplex flow control
- Supports IEEE 802.1P layer 2 priority encoding
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- LED indicator
- USB bus powered
- Robust metal housing
- Dimensions (LxWxH): ca. 73 x 72 x 23 mm

System requirements

- Linux Kernel 2.6.24 or above
- Mac OS 10.9.5 or above

- Windows 8.1/10/11
- PC or laptop with a free USB Type-A port

Package content

- USB 5 Gbps Gigabit LAN adapter
- USB 5 Gbps cable, length: ca. 0.8 m
- User manual

Images



General

Specification:	USB 5 Gbps
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Output:	4 x RJ45 jack
Input:	1 x USB 5 Gbps Type-A male

Technical characteristics

Chipset:	Realtek RTL8153
Data transfer rate:	Gigabit Ethernet up to 1 Gbps

Physical characteristics

Length:	73 mm
Width:	72 mm
Height:	23 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de