



**Flexible strain relief for cables  
model : R3.5/25**

### Dimmension

Cable cross section (A)	3.5mm
Total length (F)	25mm
Working length (E)	19.8mm
Width (B)	8,4mm
Width (D)	7,6mm
Mounting hole (C)	Max 5.6 x 5.6mm
Maximum mounting wall thickness (G)	2.5mm

### Other

Material

Hydrogenated styrene butadiene block copolymer (SEBS)  
 Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)  
 Ethylene Propylene Diene Monomer (EPDM)  
 Styrene butadiene styrene block copolymer (SBS)



