

USB-C™ cable USB 2.0 with metal sheath USB Type-C™ male to male PD 3.0 60 W 1 m silver

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port.

Durable metal jacket for optimum protection

This robust USB-C™ to USB-C™ cable features a **durable metal sheath** that offers reliable protection against external influences such as moisture, dust or damage caused by pets. Despite the sturdy sheath, the cable remains **flexible** and retains its pliability to ensure easy handling.

USB Power Delivery (USB PD 3.0) support up to 60 watt

Support for the Extended Power Range resp. USB Power Delivery 3.0 standard means that connected devices can be supplied with power, **up to 60 W** (20 V / 3 A) is possible.



Item no. 81259

EAN: 4043619812592

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors: 2 x USB 2.0 Type-C™ male
- Cable gauge:
 - 28 AWG data line
 - 23 AWG power line
- Cable with metal jacket
- Connector with metal housing
- Cable diameter: ca. 3.6 mm
- Contacts gold-plated
- Data transfer rate up to 480 Mbps
- USB Power Delivery (USB PD 3.0) support up to 60 watt (20 V / 3 A)
- Colour: silver
- Length incl. connectors: ca. 1 m

Package content

- USB cable

Images



General

Cable finishing:	metal jacketed
Specification:	USB 2.0
Style:	both sides identical

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum power:	60 W
Maximum current:	3 A
Voltage:	20.0 V

Physical characteristics

Housing material:	metal
Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 23 AWG power line
Length:	1 m
Colour:	silver
Cable diameter:	3.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de