


**1256PE** Końcówki wkrętakowe precyzyjne, trzpieniowe sześciokątne 4 mm



	art.	mm	L mm
012560021	1256PE 0,7	0.7	27
012560022	1256PE 0,9	0.9	27
012560023	1256PE 1,3	1.3	27
012560024	1256PE 1,5	1.5	27
012560025	1256PE 2,0	2.0	27

