









**Product Name // MP22SLPINRY024A5 Power Symbol  
 Illumination Vandal Resistant Switch**
 [View Product Page](#)

**// Product Description:**

- |   |  |
|---|--|
|  MP22 Range                  |  Yellow           |
|  SPDT                       |  24V             |
|  Latching                  |  AL alloy Black |
|  Power Symbol Illumination |  IP65           |

**// General Information:**

<b>Product Display Title:</b>	Power Symbol Illumination Vandal Resistant Switch
<b>Product Family:</b>	Switch Range
<b>Product Series:</b>	Vandal Resistant Switches
<b>Bezel Finish:</b>	Gloss
<b>Body Colour:</b>	Black
<b>Body Material:</b>	Aluminium
<b>Body Material Type:</b>	Metal
<b>Current Rating:</b>	5A 250V
<b>Diameter:</b>	22mm
<b>Dielectric Withstanding Voltage:</b>	1500V
<b>Durability:</b>	50,000
<b>Function:</b>	Push Button Switch
<b>Illumination Colour:</b>	Yellow
<b>Illumination Shape:</b>	Power Symbol
<b>Illumination Voltage:</b>	24V
<b>Ip Rating:</b>	IP65
<b>Lamp Type:</b>	LED
<b>Material Finish:</b>	Gloss
<b>Max Operating Temperature:</b>	55°C
<b>Min Operating Temperature:</b>	-25°C
<b>Max Panel Thickness:</b>	8mm
<b>Operating Humidity:</b>	45~85 RH(Non condensing)
<b>Panel Cut Out:</b>	22mm Diameter circle
<b>Rohs Compliant:</b>	Yes
<b>Switch Body Colour:</b>	Black
<b>Switch Body Material:</b>	Aluminium
<b>Switch Button Colour:</b>	Black
<b>Switch Button Material:</b>	Aluminium
<b>Switch Circuit:</b>	SPDT
<b>Switch Series:</b>	MP22
<b>Switch Shape:</b>	Round
<b>Switch Type:</b>	Pushbutton
<b>Switching Type:</b>	Latching
<b>Thread Size:</b>	M22

**// Product PDF Links**
 [22mm Vandal Resistant Switch](#)
**// Product 3D CAD Model Links**
 [MP22SLPINRY024A53D CAD Model](#)