

External USB 5 Gbps Hub with 13 Ports + Switch

Description

This solid USB hub by Delock with metal housing can be connected to a computer via the USB Type-A interface. It expands the computer by **13 USB Type-A ports**. Connected devices such as smartphones can be charged or data can be transferred at **5 Gbps**. Each port can be turned on or off individually by using the switches.



Item no. 63738

EAN: 4043619637386

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 13 x USB 5 Gbps Type-A female
 - 1 x 12 V DC jack
- Data transfer rate up to 5 Gbps
- 13 x LED indicator
- Robust metal housing
- Self-powered (works only with power supply)
- Dimensions (LxWxH): ca. 187 x 53 x 23 mm
- Colour: grey
- Plug & Play

Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 1.5 A
- Output: 12.0 V / 5.0 A
- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 10 mm


System requirements

- Chrome OS
- Linux Kernel 5.8 or above
- Mac OS 10.15.6 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- Hub USB 5 Gbps
- 1 x cable USB 5 Gbps A male to USB 5 Gbps B male, length ca. 1 m
- Power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 5.8.0 or above Mac OS 10.15.6 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	13 x

Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	13 x USB 5 Gbps Type-A female
Connector 3:	1 x DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Cable length:	1 m
Material:	Aluminium
Length:	187 mm
Width:	53 mm
Height:	23 mm
Switch:	13 x
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de