

USB 2.0 Cable USB Type-C™ male to male PD 3.0 100 W E-Marker 2 m red metal

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port. The integrated E-Marker chipset supports the PD 3.0 function for fast charging with a charging power of up to 100 W.

Metal housing and strain relief

Thanks to the elegant metal housing and sturdy strain relief on both sides, the cable is optimally protected against damage in everyday use.



Item no. 80041

EAN: 4043619800414

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
2 x USB Type-C™ 2.0 male
- Chipset: E-Marker
- Connector with metal housing
- Cable gauge:
28 AWG data line
22 AWG power line
- Cable diameter: ca. 4.5 mm
- Contacts gold-plated
- Connectors gold-plated
- Cable triple shielded
- Data transfer rate up to 480 Mbps
- USB Power Delivery (USB PD 3.0) support up to 100 watt (20 V / 5 A)
- Colour: black / red
- Length incl. connectors: ca. 2 m

Package content

- USB cable

Images



General

Specification:	USB 2.0
Style:	both sides identical

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ male

Technical characteristics

Chipset:	E-Marker
Data transfer rate:	480 Mbps
Maximum power:	100 W
Maximum current:	5 A
Voltage:	20.0 V

Physical characteristics

Connector finishing:	gold-plated
Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 22 AWG power line
Shielding:	triple
Length:	2 m
Colour:	black / red
Cable diameter:	4.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de