

USB Headset and Microphone Adapter with 2 x 3.5 mm Stereo Jack for Windows and Mac OS

Description

This USB adapter by Delock allows the connection of headsets and microphones with 3.5 mm stereo jack male and is especially designed for the use of video chat programs such as **Teams**, **Zoom** or **Skype for Business**.

Convenient button control

With the push-button control, calls can be accepted, dialed, held or rejected, and the microphone or webcam can be muted or switched off. The volume on the headset can be easily adjusted with the volume up and down keys.

USB DAC and ADC converter

The USB adapter has a built-in digital to analogue and analogue to digital converter. The adapter offers a sampling rate of up to **16 Bit / 48 kHz** and can therefore record and playback **audio signals in DVD quality**.

Integrated headphone amplifier

The adapter has a headphone **class G amplifier** which can also be used to connect power-intensive headsets with **up to 28 mW @ 32 ohms**.

Plug & Play

Due to USB Plug & Play the microphone is ready to use immediately, no driver installation is needed.

Please Note

Depending on the system setup and existing system configuration, the system may not support all button functions.



Item no. 66731

EAN: 4043619667314

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x 3.5 mm 3 pin stereo jack female (TRS)

- 1 x 3.5 mm 4 pin stereo jack female (TRRS)
- Sample rate: 16 Bit / 48 kHz for record and playback
- Signal-to-noise ratio (SNR): ca. 100 dB
- Total Harmonic Distortion + Noise (THD+N): 1 %
- Headphone amplifier: Class G up to 28 mW @ 32 Ohm
- Multifunction buttons: microphone mute / video camera on / off, answer call / end call / hold, volume up and down
- LED indicators: red / blue / green
- USB audio device specification 1.0
- USB HID class 1.1
- USB bus powered
- Plug & Play
- Cable length: ca. 40 cm
- Dimensions (LxWxH): ca. 50 x 21 x 14 mm

System requirements

- Mac OS 10.15.7 or above
- Windows 8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-A port

Package content

- USB adapter
- User manual

Images



General

Function:	Plug & Play
Specification:	USB 2.0
Supported operating system:	Mac OS 10.15.7 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x 3.5 mm 3 pin stereo jack female
Connector 3:	1 x 3.5 mm 4 pin stereo jack female

Technical characteristics

Voltage supply:	USB bus powered
Sample rate:	16 Bit / 48 kHz
Signal noise ratio (SNR):	ca. 100 dB

Physical characteristics

Cable length:	40 cm
LED colour:	red blue green

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de