



## BETA 7245NB BASIC leather safety shoe, water-repellent, with front protection



### Certifications and Standards



S3 FO SR RS

EN ISO 20345:2022

### Features

7245NB water-repellent leather shoe with flap, elastic steel penetration proof insole and steel toe cap for cost-effective protection.

#### FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

#### STEEL/STEEL PROTECTION

Maximum safety, low cost: our BASICS with steel toe cap and sheet provide reliable and durable protection for all pockets.

#### NEW STANDARD EN ISO 20345:2022

The shoe is S3 FO SR certified according to the latest EN ISO 20345:2022 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



#### FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



#### LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



#### PROTECTIVE FLAP AND QUICK RELEASE

The tear-off flap protects the foot from sparks and debris. Top safety thanks to quick release.



## Certifications and Standards



## Specifications

LACING:	slip-on
WEIGHT (INDICATIVE SIZE 42):	730 g
TYPE:	high

### Lightness

Water-repellent leather

### Comfort

Dual-density polyurethane

### Safety



Felt carbon

### Protections

Tip: Steel, 200 joules

Durability: Steel insole

## Coded items

	Art.	EU	UK	 mm
072451635	7245NB 35	35	2,5	228
072451636	7245NB 36	36	3,5	235
072451637	7245NB 37	37	4,5	242
072451638	7245NB 38	38	5	248
072451639	7245NB 39	39	6	255
072451640	7245NB 40	40	6,5	262
072451641	7245NB 41	41	7	268
072451642	7245NB 42	42	8	275
072451643	7245NB 43	43	9	282
072451644	7245NB 44	44	10	288
072451645	7245NB 45	45	10,5	295
072451646	7245NB 46	46	11	302
072451647	7245NB 47	47	12	308
072451648	7245NB 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

