



BETA 7342N RENEGADE microfibre shoe, water-repellent



Certifications and Standards

CE S3S FO SR HRO EN ISO 20345:2022

Features

The 7342N safety footwear focuses on comfort, style and durability, providing comfort and style throughout the working day

SAFETY WITH STYLE

The shoe that offers protection without sacrificing looks.

Thanks to the "urban" style, inspired by sports shoes, it is also perfect to wear after work.

EXTREME COMFORT

Renegade combines advanced cushioning and superior support to provide exceptional comfort throughout the working day.

Thanks to its innovative design and high performance, it ensures a smooth and comfortable walk.

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

ALL-SEASON DURABILITY

The water-repellent microfibre upper is distinguished by its outstanding resistance to stains and scratches, making it particularly suitable for year-round use. It is the ideal solution for shoes designed to last, without compromising on quality.



INNOVATIVE DESIGN

The 7342N shoe combines sporty design and modern style, highlighting an innovative outsole that ensures safety and comfort with every step



TRADITIONAL LACING

The possibility of tightening or loosening the laces allows for a secure and customised fit



MAXIMUM RESISTANCE

The rubber outsole makes the shoe extremely durable and heat-resistant up to 300°C.



Certifications and Standards

CE S3S FO SR HRO EN ISO 20345:2022



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	500 g
TYPE:	low

Lightness

- Water-repellent microfibre with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- Traditional lacing

Comfort

- EVA (ethylene vinyl acetate) midsole
- Durable nitrile rubber tread



Safety

EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules
Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
073420537	7342N 37	37	4,5	248
073420538	7342N 38	38	5	254
073420539	7342N 39	39	6	261
073420540	7342N 40	40	6,5	268
073420541	7342N 41	41	7	274
073420542	7342N 42	42	8	281
073420543	7342N 43	43	9	288
073420544	7342N 44	44	10	294
073420545	7342N 45	45	10,5	301
073420546	7342N 46	46	11	308
073420547	7342N 47	47	12	314
073420548	7342N 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

