

USB Type-C™ Adapter to HDMI and VGA with USB 3.2 Port and PD

Description

This adapter by Delock is suitable for the connection of a **VGA** monitor and an **HDMI** monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Two monitors can be operated simultaneously at the outputs. In addition, the adapter has a **USB 3.2 Type-A** interface for the use of peripherals.

USB Power Delivery (USB PD 2.0) support up to 87 watt

The docking station has a **USB Type-C™ Power Delivery port** to connect the power supply of the laptop or tablet to charge it. In addition it also supplies the USB ports with power. The docking station can also be used without a power supply.

Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 64074

EAN: 4043619640744

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x HDMI-A female
 - 1 x VGA 15 pin female
 - 1 x SuperSpeed USB 5 Gbps (USB 3.2 Gen 1) Type-A female
 - 1 x USB Type-C™ female (power supply)
- Resolution:
 - HDMI up to 3840 x 2160 @ 30 Hz
 - VGA up to 1920 x 1080 @ 60 Hz
 - (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Input power: 1 x USB Type-C™ female max. 87 W
- Metal housing
- Cable length without connectors: ca. 12 cm
- Colour: grey
- Dimensions (LxWxH): ca. 65 x 40 x 16 mm

System requirements

- Android 9.0 or above
- Mac OS 10.14.2 or above
- Windows 8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI and VGA adapter
- User manual

Images



General

Supported operating system:	Android 9.0 or above Mac OS 10.14.2 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11
-----------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------

Interface

Connector:	1 x USB Type-C™ male 1 x USB Type-C™ female 1 x HDMI-A female 1 x USB 5 Gbps Type-A female 1 x VGA 15 pin female
------------	------------------------------------------------------------------------------------------------------------------------------

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz 1920 x 1080 @ 60 Hz
----------------------------	--------------------------------------------

Physical characteristics

Housing material:	metal
Cable length:	12 cm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de