



## BETA 7243NC BASIC leather safety shoe, water-repellent



### Certifications and Standards



S3 FO SR RS

EN ISO 20345:2022

### Features

Smooth water-repellent leather 7243NC footwear with anti-puncture foil and steel toe cap for cost-effective protection.

#### FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

#### STEEL/STEEL PROTECTION

Maximum safety, low cost: our BASICS with steel toe cap and sheet provide reliable and durable protection for all pockets.

#### NEW STANDARD EN ISO 20345:2022

The shoe is S3 FO SR certified according to the latest EN ISO 20345:2022 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



#### FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



#### LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



#### PROTECTIVE GUSSET AND QUICK RELEASE

Leather gusseted tongue protects against annoying seepage of liquids and debris. Top safety thanks to quick release.



## Certifications and Standards



## Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	700 g
TYPE:	high

### Lightness

Water-repellent leather

### Comfort

Dual-density polyurethane

### Safety



Felt carbon

### Protections

Tip: Steel, 200 joules

Durability: Steel insole

## Coded items

	Art.	EU	UK	 mm
072431635	7243NC 35	35	2,5	228
072431636	7243NC 36	36	3,5	235
072431637	7243NC 37	37	4,5	242
072431638	7243NC 38	38	5	248
072431639	7243NC 39	39	6	255
072431640	7243NC 40	40	6,5	262
072431641	7243NC 41	41	7	268
072431642	7243NC 42	42	8	275
072431643	7243NC 43	43	9	282
072431644	7243NC 44	44	10	288
072431645	7243NC 45	45	10,5	295
072431646	7243NC 46	46	11	302
072431647	7243NC 47	47	12	308
072431648	7243NC 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

