

# USB 5 Gbps Hub with 7 Ports + 1 Fast Charging Port + 1 USB-C™ PD 3.0 Port with Switch and Illumination

## Description

This solid USB hub by Delock with **metal housing** can be connected to a computer via the USB Type-A interface. It expands the computer by **7 USB Type-A** ports. Connected devices such as smartphones can be charged or data can be transferred at **5 Gbps**.

## Additional fast charging port and USB-C™ PD 3.0 port

Another USB Type-A port offers the possibility to charge devices, such as smartphones with up to **2.4 A**.

The USB Type-C™ PD port offers up to **12 V and 2.25 A** output power, so laptops can also be charged.

## LED illumination and switch

Each port can be turned on or off individually by using the switches. In addition, each USB Type-A port has a frame that lights up as soon as the port is activated.



**Item no. 63264**

EAN: 4043619632640

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 5 Gbps Type-B female
  - 7 x USB 5 Gbps Type-A female
  - 1 x USB Type-A charging port (max. 5 V / 2.4 A)
  - 1 x USB Type-C™ female PD 3.0 (max. 12 V / 2.25 A)
  - 1 x 12 V DC jack
- Chipset: Genesys Logic GL3510, GL888F, IP6528AC
- Data transfer rate up to 5 Gbps
- LED illumination on the USB Type-A ports
- Robust metal housing
- Power supply: Self-powered
- Dimensions (LxWxH): ca. 144 x 46 x 21 mm
- Colour: grey
- Plug & Play

## Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: SAW48C-120-3000G
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 1.3 A
- Output voltage / Output current / Output power: 12.0 V / 3.0 A / 36.0 W
- Average active efficiency: 89.1 %
- Efficiency at low load (10 %): 86.0 %
- No-load power consumption: 0.09 W
- Power supply cable length: ca. 1.5 m
- DC power connector: 5.5 x 2.1 mm
- Ground outside, plus inside

---

## System requirements

- Chrome OS
- Linux Kernel 3.18 or above
- Mac OS 10.15.3 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

---

## Package content

- Hub USB 5 Gbps
- 1 x cable USB 5 Gbps Type-A male to USB 5 Gbps Type-B male, length ca. 80 cm
- External power supply
- User manual

---

## Images



## General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 3.18 or above Mac OS 10.15.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	8 x

## Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	7 x USB 5 Gbps Type-A female
Connector 3:	1 x USB Type-A charging port (max. 5 V / 2.4 A)
Connector 4:	1 x 12 V DC jack
Connector 5:	1 x USB Type-C™ female PD 3.0 (max. 12 V / 2.25 A)

## Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

## Physical characteristics

Cable length:	80 cm
Material:	Aluminium
Length:	144 mm
Width:	46 mm
Height:	21 mm
Switch:	8 x
Colour:	grey

## Power supply

Power supply type:	<b>Power supply specification</b> Euro wall power supply
Model identifier:	<b>Power supply specification</b> SAW48C-120-3000G
Input voltage:	<b>Power supply specification</b> 100 - 240 V
Input AC frequency:	<b>Power supply specification</b> 50 / 60 Hz
Input current:	<b>Power supply specification</b> 1.3 A
Output voltage / Output current / Output power:	<b>Power supply specification</b> 12.0 V / 3.0 A / 36.0 W
Average active efficiency:	<b>Power supply specification</b> 89.1 %
Efficiency at low load (10 %):	<b>Power supply specification</b> 86.0 %
No-load power consumption:	<b>Power supply specification</b> 0.09 W
Power supply connector:	<b>Power supply specification</b> DC male 5.5 mm x 2.1 mm Ground outside, plus inside
Cable length of power supply:	<b>Power supply specification</b> 1.5 m

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de